




Serie 2808 - snap-open along inner and outer radius



R [mm]	K	T [mm]
100	465	056
125	550	056
150	620	056
175	700	056
200	780	056
250	940	056

Part No. structure



- Color
- Outer radius
- Inner radius
- Width
- Series

Bi [mm]	Ba [mm]	AR [mm]	IR [mm]	R 100 mm 2808....	R 125 mm 2808....	R 150 mm 2808....	R 175 mm 2808....	R 200 mm 2808....	R 250 mm 2808....	Weights [kg/m]
50	81	400	329,5	.05.100/400	.05.125/400	.05.150/400	.05.175/400	.05.200/400	.05.250/400	≈ 1,76
68	99	400	311,5	.06.100/400	.06.125/400	.06.150/400	.06.175/400	.06.200/400	.06.250/400	≈ 1,87
75	106	400	304,5	.07.100/400	.07.125/400	.07.150/400	.07.175/400	.07.200/400	.07.250/400	≈ 1,92
87,5	118,5	400	292	.087.100/400	.087.125/400	.087.150/400	.087.175/400	.087.200/400	.087.250/400	≈ 1,99
100	131	400	279,5	-	-	.10.150/400	.10.175/400	.10.200/400	.10.250/400	≈ 2,07
108	139	400	271,5	-	-	-	.11.175/400	.11.200/400	.11.250/400	≈ 2,12
125	156	400	254,5	-	-	-	.12.175/400	.12.200/400	.12.250/400	≈ 2,22
137,5	168,5	400	242	-	-	-	-	-	.137.250/400	≈ 2,30
150	181	400	229,5	-	-	-	-	-	.15.250/400	≈ 2,38

50	81	500	429,5	.05.100/500	.05.125/500	.05.150/500	.05.175/500	.05.200/500	.05.250/500	≈ 1,76
68	99	500	411,5	.06.100/500	.06.125/500	.06.150/500	.06.175/500	.06.200/500	.06.250/500	≈ 1,87
75	106	500	404,5	.07.100/500	.07.125/500	.07.150/500	.07.175/500	.07.200/500	.07.250/500	≈ 1,92
87,5	118,5	500	392	.087.100/500	.087.125/500	.087.150/500	.087.175/500	.087.200/500	.087.250/500	≈ 1,99
100	131	500	379,5	.10.100/500	.10.125/500	.10.150/500	.10.175/500	.10.200/500	.10.250/500	≈ 2,07
108	139	500	371,5	-	.11.125/500	.11.150/500	.11.175/500	.11.200/500	.11.250/500	≈ 2,12
125	156	500	354,5	-	.12.125/500	.12.150/500	.12.175/500	.12.200/500	.12.250/500	≈ 2,22
137,5	168,5	500	342	-	-	.137.150/500	.137.175/500	.137.200/500	.137.250/500	≈ 2,30
150	181	500	329,5	-	-	.15.150/500	.15.175/500	.15.200/500	.15.250/500	≈ 2,38

50	81	600	529,5	.05.100/600	.05.125/600	.05.150/600	.05.175/600	.05.200/600	.05.250/600	≈ 1,76
68	99	600	511,5	.06.100/600	.06.125/600	.06.150/600	.06.175/600	.06.200/600	.06.250/600	≈ 1,87
75	106	600	504,5	.07.100/600	.07.125/600	.07.150/600	.07.175/600	.07.200/600	.07.250/600	≈ 1,92
87,5	118,5	600	492	.087.100/600	.087.125/600	.087.150/600	.087.175/600	.087.200/600	.087.250/600	≈ 1,99
100	131	600	479,5	.10.100/600	.10.125/600	.10.150/600	.10.175/600	.10.200/600	.10.250/600	≈ 2,07
108	139	600	471,5	.11.100/600	.11.125/600	.11.150/600	.11.175/600	.11.200/600	.11.250/600	≈ 2,12
125	156	600	454,5	-	.12.125/600	.12.150/600	.12.175/600	.12.200/600	.12.250/600	≈ 2,22
137,5	168,5	600	442	-	.137.125/600	.137.150/600	.137.175/600	.137.200/600	.137.250/600	≈ 2,30
150	181	600	429,5	-	-	.15.150/600	.15.175/600	.15.200/600	.15.250/600	≈ 2,38



Interior separation - For this Series the interior separation elements of Series E4.32 E4.1 may be used (except side-plates) ► page 7.38



TwisterChain®-System
Inner height: 28-56 mm

Phone +49- (0) 22 03-96 49-800
Fax +49- (0) 22 03-96 49-222

