















Tragarmsystem CP 180

	drehbar/neigbar	starr	Länge mm	Gewicht kg	Farbe RAL	Gehäuseteil CP 180/120	Mittelteil CP 180	Wandteil CP 180	
									
Best.-Nr.									
Befestigung CP 120 für Tragarmanschluss Ø 130 mm									
	-	■	-	0,7	7035	6212.320	-	-	
Kupplung CP 120 für Tragarmanschluss Ø 130 mm									
	■	-	-	2,0	7035	6212.300	-	-	
Tragprofil CP 180/120						CP 120 ¹⁾	CP 180	CP 180	
	geschlossen	-	-	250	2,6	7035	6212.025	-	-
		-	-	500	5,2		6212.050	6218.050	6218.050
		-	-	1000	10,5		6212.100	6218.100	6218.100
		-	-	2000	21		6212.200	6218.200	6218.200
	offen	-	-	500	5,8	7035/ 7024	6212.150	6218.150	6218.150
		-	-	1000	11,6		6212.110	6218.110	6218.110
		-	-	2000	23,2		6212.210	6218.210	6218.210
Adapter für Tragarm-Kombination CP 180/120									
	siehe Seite 159	-	■	-	1,5	7035	6218.640	-	-
Winkelstück 90° CP 180									
	-	■	-	3,6	7035/ 7024	6218.600	-	6218.600	
Zwischengelenk CP 180									
	■	-	-	10,3	7035/ 7024	-	6218.620	-	
Aufsatzgelenk CP 180									
	Abgang horizontal	■	-	18,0	7035/ 7024	-	-	6218.700	
Wandgelenk CP 180									
	Abgang horizontal	■	-	13,0	7035/ 7024	-	-	6218.740	
Wand-/Bodenbefestigung CP 180, klein									
	-	■	-	5,0	7035	-	-	6218.820	
Montage-Element CP 120/180 für Signalsäule									
	Nur für 6218.600, 6218.700, siehe Seite 720	-	■	-	0,1	7024	6212.900	-	6212.900

¹⁾ Gewichtsangaben und Grafiken für CP 120, siehe Seite 151