

Divider panels/partitions

Divider panel

for TS

For shielding individual enclosure cells. Thanks to the symmetry of the frame system, the divider panel can also be used at the rear. All-round, double fold for stability and to hold the seal.

Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted.

For mounting on the outer mounting level. This leaves the inner level free for further population.

Material:

- Sheet steel, 1.5 mm

Surface finish:

- Zinc-plated

Protection category to IEC 60 529:

- IP 54

Supply includes:

- Assembly parts

Note:




- The divider panel can also be fitted at the rear, allowing e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/finished off with a cover (see page 540).



Accessories:

- Cover with door, see page 540
- Baying bracket, vertical, 8800.470 for enclosures with fitted divider panel, see page 546

For enclosures		Model No.
Height mm	Depth mm	
1800	400	8609.840
1800	500	8609.850
1800	600	8609.860
2000	400	8609.040
2000	500	8609.050
2000	600	8609.060
2000	800	8609.080
2200	600	8609.260



Partition

for TS-IT

For rack mounting, suspended between two enclosures. With three Ø 40 mm holes in all 4 corner areas for the insertion of cables, conduits etc. Drilled holes may be sealed with the enclosed stepped collars. For cable entry, simply cut off at a suitable level to match the required cross-section.

Material:

- Partition: Sheet steel
- Stepped collar: Plastic to UL 94-HB

Surface finish:

- Partition: Zinc-plated

For enclosures		Model No.
Height mm	Depth mm	
2000	1000	7831.723
2000	1200	7831.724

Note:

- Not suitable for use in conjunction with a baying seal. Any existing seals must be removed prior to installation



Accessories:

- Baying clamp 8800.490, see page 544

