

# Doors/locks

## Door, internal



### Perforated mounting strip

#### for AE stainless steel

For vertical mounting on the threaded bolts of the door, for attaching

- Support strips for AE, see page 575
- Door stay 2519.000, see page 578

3.7 mm diameter hole on a 25 mm DIN pitch pattern

#### Material:

- Sheet steel

#### Surface finish:

- Zinc-plated

#### Supply includes:

- Packs of 20 (nuts and serrated washers included)

To match AE	Length mm	Model No.
1012.600, 1014.600	698	<b>2310.076</b>
1016.600, 1018.600	938	<b>2310.100</b>
1017.600, 1019.500, 1019.600	1138	<b>2310.120</b>



#### Accessories:

- Screws, see page 625



### Utility lectern

For programming units etc. Prepared for mounting on the tubular door frame of TS, SE, CM, PC or on any sufficiently large surface.

When required for servicing, it folds down quickly with a maximum support area, and after use is stowed between the tubular door frames in a space-saving design.

#### Load capacity:

- max. 30 kg.

#### Material:

- Sheet steel

#### Colour:

- RAL 7035

Support area		For door width mm	Model No.
Width mm	Depth mm		
413	400	600	<b>4638.600</b>
613	400	800	<b>4638.800</b>



### Wiring plan lectern

Holds wiring plans during fault finding and maintenance work. The wiring plan lecterns can be bayed according to the door width. For mounting on the tubular door frame.

#### Material:

- Utility lectern: Polypropylene
- Mounting bracket: Die-cast zinc

#### Colour:

- Similar to RAL 7035

#### Supply includes:

- Wiring plan lectern (width 210 mm)
- Assembly parts

For enclosures	Packs of	Model No.
TS, SE, CM, TP, PC	1 pc(s).	<b>4120.000</b>

For door width mm	Required/possible number of wiring plan lecterns	
	min.	Max.
400	1	1
500	1	1
600	2	2
800	2	3
1000	3	3



### CD/DVD box

For fixing to all flat, clean surfaces with double-sided adhesive tape.

#### Capacity:

- Max. 10 CDs/DVDs

#### Material:

- Polyamide

#### Colour:

- RAL 7033

Packs of	Model No.
1 pc(s).	<b>2446.000</b>