

Cable management

Cable gland



Cable gland, brass

Benefits:

- Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage
- Clamping membranes for even tightening and strain relief which protects the cables

Material:

- Brass
- Seal: TPE/NBR

Surface finish:

- Nickel-plated

Protection category IP to IEC 60 529:

- IP 68 (1 bar, 30 min.)

Approval:

- VDE tested to EN 50 262

Size	Cable diameter mm	Packs of	Model No.
M12 x 1.5	3 – 7	15 pc(s).	2411.800
M16 x 1.5	4.5 – 10	15 pc(s).	2411.810
M20 x 1.5	7 – 13	10 pc(s).	2411.820
M25 x 1.5	10 – 17	10 pc(s).	2411.830
M32 x 1.5	13 – 21	5 pc(s).	2411.840
M40 x 1.5	19 – 28	4 pc(s).	2411.850
M50 x 1.5	25 – 35	2 pc(s).	2411.860
M63 x 1.5	35 – 48	1 pc(s).	2411.870

 **Possible alternative:**

- Hygienic Design cable gland, see page 659



Cable gland, polyamide

Benefits:

- Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage
- Clamping membranes for even tightening and strain relief which protects the cables

Material:

- Polyamide 6
- Seal: Neoprene

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 68 (1 bar, 30 min.)

Approval:

- VDE tested to EN 50 262

Size	Cable diameter mm	Packs of	Model No.
M12 x 1.5	2.5 – 6.5	50 pc(s).	2411.600
M16 x 1.5	4.5 – 10	50 pc(s).	2411.610
M20 x 1.5	7 – 13	50 pc(s).	2411.620
M25 x 1.5	10 – 17	25 pc(s).	2411.630
M32 x 1.5	17 – 25	15 pc(s).	2411.640
M40 x 1.5	22 – 33	5 pc(s).	2411.650
M50 x 1.5	28 – 38	5 pc(s).	2411.660
M63 x 1.5	32 – 44	3 pc(s).	2411.670