

Air/water heat exchangers

Wall-mounted, useful cooling output 1750 W, water-carrying parts V4A (1.4571)

Model No. SK	3373.504 ¹⁾		3373.104 ¹⁾	Page
Thermostat (factory setting +35°C)	e-Comfort controller	■	–	
	Basic controller	–	■	
Useful cooling output	L 35 W 10, 400 l/h	1750 W		
Rated operating voltage V, Hz	230, 1~, 50/60			
Dimensions mm	W x H x D 400 x 950 x 140			
Rated current max.	0.38 A/0.43 A			
Pre-fuse T	4.0 A			
Cooling medium	Water (for specifications see Internet; user manual)			
Water inlet temperature	+1°C to +30°C			
Permissible operating pressure p. max.	1 to 10 bar			
Operating temperature and setting range	+1°C to +70°C			
Protection category to IEC 60 529	IP 55 ²⁾			
Duty cycle	100%			
Type of connection	Plug-in terminal strip			
Water connection	Quick-release fastener system ³⁾			
Weight	20 kg			
Air throughput of fan (unimpeded air flow)	600/625 m ³ /h			
Accessories	Packs of			
Door-operated switch	1	4127.010	4127.010	684
SK BUS system	1	3124.100	–	477
Interface board	1	3124.200	–	477
Condensate hose	1	3301.612	3301.612	485
Flow regulator valve	1		see page 486	

¹⁾ Extended delivery times.

²⁾ IP 65 available on request.

³⁾ Threaded adaptor for quick-release fastener available on request.

Special voltages available on request. We reserve the right to make technical modifications.

Wall-mounted, useful cooling output 2500 W, water-carrying parts V4A (1.4571)

Model No. SK	3374.504 ¹⁾		3374.104 ¹⁾	Page
Thermostat (factory setting +35°C)	e-Comfort controller	■	–	
	Basic controller	–	■	
Useful cooling output	L 35 W 10, 400 l/h	2500 W		
Rated operating voltage V, Hz	230, 1~, 50/60			
Dimensions mm	W x H x D 400 x 950 x 140			
Rated current max.	0.57 A/0.78 A			
Pre-fuse T	4.0 A			
Cooling medium	Water (for specifications see Internet; user manual)			
Water inlet temperature	+1°C to +30°C			
Permissible operating pressure p. max.	1 to 10 bar			
Operating temperature and setting range	+1°C to +70°C			
Protection category to IEC 60 529	IP 55 ²⁾			
Duty cycle	100%			
Type of connection	Plug-in terminal strip			
Water connection	Quick-release fastener system ³⁾			
Weight	20 kg			
Air throughput of fan (unimpeded air flow)	700/730 m ³ /h			
Accessories	Packs of			
Door-operated switch	1	4127.010	4127.010	684
SK BUS system	1	3124.100	–	477
Interface board	1	3124.200	–	477
Condensate hose	1	3301.612	3301.612	485
Flow regulator valve	1		see page 486	

¹⁾ Extended delivery times.

²⁾ IP 65 available on request.

³⁾ Threaded adaptor for quick-release fastener available on request.

Special voltages available on request. We reserve the right to make technical modifications.