


## 2/2 way solenoid valve normally closed or normally open


**type 32, stainless steel body (AISI 303)  
direct operated, DN 1,5 – 3,0mm, G1/8**



normally closed NC



normally open NO



<b>SPECIFICATION</b>	
<b>general</b>	
type of construction	2/2-poppet valve, normally closed NC or normally open NO, coil 360° rotatable
operator	solenoid, or optional by manual override
ports	G1/8
ambient temperature	-5°C to +50°C, higher allowed ambient temperatures on request
fluid temperature	dependent on sealing material and coil
viscosity	max. 37 mm²/s (cst) or 5° E
material	Body and tube: stainless steel AISI 303 Inner parts : stainless steel sealing: see type selection
mounting	2 threads M3
installation	in any position, preferable vertical fixed solenoid coil
unit of supply	without connector
<b>electrical data</b>	
voltage	DC voltage or AC voltage
standard voltage	24V DC, 24V AC, 230V AC
special voltage on request	6V-200V DC, 12V-240V, 50Hz or 60Hz
acceptable voltage tolerance	+/- 10%
power consumption	see specifications at solenoid coils
coil type	temperature class F (155°C), winding class H (180°C)
acceptable voltage tolerance	+/- 10%
protection class	IP65 according DIN EN 60529 (DIN 40050) with correctly mounted connector
<b>pneumatic – hydraulic</b>	
flow medium	all liquids and gases, which don't attack the used material
max. body housing pressure	PN 40 (bar)
response time	12 – 20ms
special equipment on request	coil type with cable, coil EExmIIT5, coils for temperature class H (180°C), other sealing materials

E & OE: We reserve the right to change design, dimensions or materials without notice.

type 32A, normally closed										
type * (order-nr.)	NW DN (mm)	maximum differential pressure in bar **								
		coil C1DA		coil C2DA		coil C3AA		coil CXFA		
		~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	
32A – 1.15–C...	1,5	20	10	25	16	30	25	25	12	0,082
32A – 1.20–C...	2,0	10	2	16	8	25	15	12	3,5	0,133
32A – 1.25–C...	2,5	5	0,6	10	3,5	14	8	6	1	0,195
32A – 1.30–C...	3,0	3,5	-	6	1,5	9	3	4	0,5	0,250

\* Type designation (order-nr.) must be completed with sealing material, short circuit ring, coil and supply voltage. (see order code)

\*\* At DC voltage all pressure specifications apply to a fluid temperature up to 80 °C. At higher fluid temperatures, the maximum differential pressure will be reduced by 0,5% / °C. All specifications refer to fluids with a maximum viscosity of 37 cSt. (5°E). Higher viscosities cause extended response time and need a special specification of the valve

sealing material	Code	fluid temperature	applicable for
NBR (Perbunan)	B	max. 80 °C	neutral gases and liquids
EPDM	E	max. 130 °C	hot water, steam, not for oil and grease
FPM	V	max. 130 °C	oil, petrol, oxygen, acids and bases

standard voltage	Code
24V = DC	02400
24V ~ (50Hz)	02450
230V ~ (50Hz)	23050

coil power consumption at 20 °C, protection class, interface					
coil type	inrush power ~ (50Hz) VA	rated power ~ (50Hz) VA	power = (DC) (W)	protection class with/without connector	interface
C1DA	7,5	5	3,0	IP65 / IP00	Connector (DIN 43650) type B industrial standard
C2DA	12,5	9	6,5	IP65 / IP00	Connector (DIN 43650) type B industrial standard
C3AA	15	11	6,3	IP65 / IP00	Connector DIN EN 175301 – 803 (DIN 43650), type A
CXFA	5,1	5,1	5,0	IP65	Coil explosion proof according to ATEX II 2G Ex mb II T4 II 2D ExtDA21 IP65 T130°C cable length 3 meter


ORDER CODE	32 B - 1 V 20 G Z - A C3AA 23050	
	<p>type function ports seal material nominal size seat</p>	
type	type 32, medium contacting metal parts AISI 303 and AISI 430 FR	
function	A = normally closed, B = normally open	
ports	1 = G1/8	
seal material	B = NBR (Perbunan), E = EPDM, V = FPM	
nominal size seat	15 = 1,5 mm, 20 = 2,0 mm, 25 = 2,5 mm, 30 = 3,0 mm	
throw off spring	only normally open – see specific type (B, F, G)	
stroke compensation spring	Z = only normally open	
short circuit ring	A = copper short circuit ring, X = without short circuit ring, B = solid silver C = copper gold-plated, D = copper chemical nickel-plated	
coil type	see specifications of the particular coil	
supply voltage	always 5-digit, see code of standard voltage	

type 32B, normally open										
type * (order-nr.)	NW DN (mm)	maximum differential pressure in bar **								
		coil C1DA		coil C2DA		coil C3AA		coil CXFA		
		~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	
32B-1.15BZ-.C1DA	1,5	5	5						0,082	
32B-1.20BZ-.C1DA	2,0	3,5	3,5						0,133	
32B-1.25BZ-.C1DA	2,5	2,0	2,0						0,195	
32B-1.30BZ-.C1DA	3,0	2,5	-						0,250	
32B-1.15FZ-.C2DA	1,5			10	10				0,082	
32B-1.20FZ-.C2DA	2,0			5,5	5,5				0,133	
32B-1.25FZ-.C2DA	2,5			3,5	3,5				0,195	
32B-1.30FZ-.C2DA	3,0			4,0	-				0,250	
32B-1.15GZ-.C3AA	1,5					13	13		0,082	
32B-1.20GZ-.C3AA	2,0					8	8		0,133	
32B-1.25GZ-.C3AA	2,5					5	5		0,195	
32B-1.30GZ-.C3AA	3,0					5	-		0,250	
32B-1.15BZ-.CXFA	1,5							5	5	0,082
32B-1.20BZ-.CXFA	2,0							3,5	3,5	0,133
32B-1.25BZ-.CXFA	2,5							2,0	2,0	0,195
32B-1.30BZ-.CXFA	3,0							2,5	-	0,250

\* Type designation (order-nr.) must be completed with sealing material, short circuit ring, coil and supply voltage. (see order code)

\*\* All specifications refer to fluids with a maximum viscosity of 37 cst. (5°E).

Higher viscosities cause extended response time and need a special specification of the valve.



### **Dimension table for type 32 in mm, weight approx. in g**

Dimension table for type 32 M.M.M, weight approx. 11.9 g																				
with coil	N	n	O	M	H		h	G	I	L	D	d	weight (g)							
					type 32A	type 32B							type 32A	type 32B						
C1DA	15	15	M3	49	57	58.5	8	G 1/8	6	30	22	20	142	142						
C2DA													142	142						
C3AA				53.5							30		197	197						
CXFA											22		392	392						