

Interior installation

Installation kits/accessories for component shelves



TS punched section with mounting flange, 17 x 73 mm

as installation kit for component shelves

Simply locate and secure. One pack is sufficient for 2 component shelves.

Load capacity:

- 100 kg surface load, static

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

Installation in enclosure depth mm	Packs of	Model No.
500	4 pc(s).	8612.050
600	4 pc(s).	8612.060
800	4 pc(s).	8612.080
1000	4 pc(s).	8612.000
1200	4 pc(s).	8612.020



Adaptor for L-shaped mounting angles

for TS network enclosures

For mounting component shelves and slide rails on L-shaped mounting angles.

Material:

- Sheet steel

Supply includes:

- Assembly parts

Packs of	Model No.
4 pc(s).	7827.300



Telescopic slides

for component shelves in TS and for upgrading existing DK-TS applications

Fixed component shelves are easily converted to full withdrawal. For this purpose, the existing fastening bolts or mounting rails (heavy-duty version) are exchanged for the telescopic slides.

Technical specifications:

- For installation and locking on a 25 mm pitch pattern in the enclosure depth

Load capacity:

- 50 kg/100 kg per set

Material:

- Sheet steel

Surface finish:


- Zinc-plated

Load capacity 50 kg

For component shelf depth mm	Packs of	Model No.
400	2 pc(s).	7061.000
500	2 pc(s).	7081.000
600	2 pc(s).	7161.000
700	2 pc(s).	7161.700

Load capacity 100 kg

For component shelf depth mm	Packs of	Model No.
400	2 pc(s).	7064.000
500	2 pc(s).	7065.000
600	2 pc(s).	7066.000
700	2 pc(s).	7066.700



- 1 Assembly bolts
- 2 Mounting rails
- 3 Telescopic slides