


Keyboard housings, standard sizes



Material:

Enclosure:
Extruded aluminium section
Corner pieces:
Die-cast zinc
Corner protectors:
Self-extinguishing plastic
Rear panel:
Aluminium

Surface finish:

Enclosure and rear panel:
Natural-anodised
Corner pieces:
Powder-coated in finely-textured
RAL 7035
Corner protectors:
Dyed similar to RAL 7024

Protection category:

IP 65 to EN 60 529/09.2000
(if the openings in the enclosure are covered or sealed in accordance with the protection category).



Accessories:

Operating housings, see page 194.

Detailed drawing, see page 1202.

B
1.4

Comfort Panel

		Packs of	Keyboard housing			
To fit front panels	Width x height mm		482.6 (19") x 155 (3.5 U)	482.6 (19") x 177 (4 U)	482.6 (19") x 155 (3.5 U)	482.6 (19") x 177 (4 U)
Installation depth			74		113	
Width (B) mm			591		591	
Height (H) mm			264	286	264	286
Depth (T) mm			92		131	
Cable tube cut-out			Model No. CP			
Without		1	6371.180	6371.200	6371.250	6371.270
With		1	6371.190¹⁾	6371.210¹⁾	6371.260¹⁾	6371.280¹⁾
Weight (kg)			5.7	5.9	8.0	8.2
Rear panel	Screw-fastened		■	■	■	■

¹⁾ Extended delivery times.



USB/RJ 45 extension
Model No. see page 1150.



Frame connector, adjustable
for Comfort Panel,
Model No. see page 977.