



### TS support strips

#### Installation options:

- On the vertical and horizontal TS enclosure section
  - On the outer mounting level, all-round, at the same height
  - On the inner mounting level, all-round, height-offset
- On the tubular door frame TS, ES
- On the perforated door strip CM, TP
- On the ES system punchings, in the enclosure depth

#### Material:

Sheet steel, zinc-plated, passivated

#### Supply includes:

Assembly screws.




#### For the outer mounting level

For enclosure width/depth mm	Length mm	Packs of	Model No. TS
300	240	20	<b>8800.125</b>
400	340	20	<b>4694.000</b>
500	440	20	<b>4695.000</b>
600	540	20	<b>4696.000</b>
800	740	20	<b>4697.000</b>




#### Accessories:

Screws, see page 1011.  
Cable tie for quick assembly SZ 2597.000, see page 1066.



#### For the inner mounting level and for mounting on doors

For enclosure width/depth mm	For door width mm	Length mm	Packs of	Model No. TS
–	400	290	20	<b>4594.000</b>
400	500	390	20	<b>4309.000</b>
500	600	490	20	<b>4596.000</b>
600	–	590	20	<b>8800.130</b>
–	800	690	20	<b>4598.000</b>
800	900	790	20	<b>4579.000</b>
–	1000	890	20	<b>4599.000</b>



### TS assembly block

Installation in the vertical TS enclosure sections for mounting PS-compatible individual components.

#### Material:

Die-cast zinc

#### Supply includes:

Assembly screws.

Packs of	Model No. TS
4	<b>8800.310</b>



#### Possible alternative:

Snap-on nut, see page 1005.



### Adaptor rail

#### for PS compatibility

Installation in the vertical TS enclosure sections (across the entire enclosure height or in sub-sections) to create compatibility with:

- PS punched rail, 23 x 23 mm
- PS punched section without mounting flange, 23 x 73 mm
- PS punched section with mounting flange, 23 x 73 mm

#### Material:

Sheet steel, zinc-plated, passivated

#### Supply includes:

Assembly screws.

For enclosure height mm	Packs of	Model No. TS
1800	4	<b>8800.380</b>
2000	4	<b>8800.300</b>
2200	4	<b>8800.320</b>





#### Accessories:

Screws, see page 1011.



#### Possible alternative:

Snap-on nut, see page 1005.



**German patent no. 19 647 781**  
**European patent no. 0 939 990**  
**with validity for FR, GB, IT, SE**  
**US patent no. 6,206,494**  
**Australian patent no. 727 880**  
**Chinese patent no. ZL 971 997 31.4**