



PS punched section with mounting flange 23 x 73 mm

for TS, ES

Variable, with 5 rows of holes for universal skeleton structures or partial assembly. Simply locate into the system punchings and secure.

Installation options:

- On the vertical TS enclosure section – Via adaptor rail for PS compatibility
- On the horizontal TS enclosure section
- On the ES system punchings, in the enclosure depth

Material:

Sheet steel, zinc-plated, passivated

Supply includes:

Assembly screws.



Installation in enclosure width/depth TS mm	Packs of	Model No. PS
400	4	8800.640
500	4	8800.650
600	4	4364.000
800	4	4365.000
1000	4	4373.000
1200	4	4367.000

Installation in enclosure depth ES, AP universal console, CS modular enclosures mm	Packs of	Model No. PS
400	4	4369.000
500	4	4370.000
600	4	4371.000
800	4	4372.000



Also required:

Adaptor rail for PS compatibility (when mounting on the vertical enclosure section), see page 997.



C rails 30/15

to EN 60 715

for TS, ES

Installation options:

- On the vertical TS enclosure section – Via snap-on nut TS 8800.808 (Fig. left) – Via adaptor rail for PS compatibility
- On the horizontal TS enclosure section (Fig. right)
- On the ES system punchings

Material:

Sheet steel, zinc-plated, passivated



For enclosure width/depth mm	Length mm	Packs of	Model No. PS
500	455	6	4943.000
600	555	6	4944.000
800	755	6	4945.000
1000	955	6	4946.000
1200	1155	6	4947.000



Accessories:

Cable clamps, see page 1064.
Support bracket or spacer, see page 1008.
Quick-assembly block, see page 1008.
Snap-on nut M8, TS 8800.808, see page 1005.
Adaptor rail, see page 997.



Possible alternative:

Rail for EMC shielding bracket and strain relief, see page 1031.