











# RiLine60 connection system

## Busbar connection adaptor 63 A/125 A/250 A/800 A, cable outlet top

						
Design	Packs of	3-pole	3-pole	3-pole	3-pole	Page
Rated current up to		63 A	125 A	250 A	800 A	
Rated operating voltage		690 V~	690 V~	690 V~	690 V~	
Cable outlet at the top		■	■	■	■	
Connection of round conductors mm <sup>2</sup> ● fine-wire with wire end ferrule ● multi-wire ● solid		2.5 – 10 2.5 – 10 2.5 – 10	10 – 25 16 – 35 –	35 – 120 35 – 120 –	95 – 185 95 – 300 –	
Clamping area for laminated copper bars W x H mm		–	10 x 7.8	18.5 x 15.5	33 x 20	
Width mm		20	55	90	129	
Height mm		215	210	210	246	
Approvals		UL	UL	UL	UL	
For bar systems with centre-to-centre spacing mm		60	60	60	60	
For bar thickness mm		5/10	5/10	5/10	5/10	
<b>Model No. SV</b>	1	<b>9342.200</b>	<b>9342.230</b>	<b>9342.260</b>	<b>9342.290</b>	
<b>Accessories</b>						
Laminated copper bars		–	■	■	■	314

## Busbar connection adaptor 63 A/125 A/250 A/800 A, cable outlet bottom

								
Design	Packs of	3-pole				4-pole		Page
Rated current up to		63 A	125 A	250 A	800 A	125 A	250 A	
Rated operating voltage		690 V~	690 V~	690 V~	690 V~	690 V~	690 V~	
Cable outlet at the bottom		■	■	■	■	■	■	
Connection of round conductors mm <sup>2</sup> ● fine-wire with wire end ferrule ● multi-wire ● solid		2.5 – 10 2.5 – 10 2.5 – 10	10 – 25 16 – 35 –	35 – 120 35 – 120 –	95 – 185 95 – 300 –	10 – 25 16 – 35 –	35 – 120 35 – 120 –	
Clamping area for laminated copper bars W x H mm		–	10 x 7.8	18.5 x 15.5	33 x 20	10 x 7.8	18.5 x 15.5	
Width mm		20	55	90	129	75	118	
Height mm		215	210	210	246	270	270	
Approvals		UL	UL	UL	UL	UL	UL	
For bar systems with centre-to-centre spacing mm		60	60	60	60	60	60	
For bar thickness mm		5/10	5/10	5/10	5/10	5/10	5/10	
<b>Model No. SV</b>	1	<b>9342.210</b>	<b>9342.240</b>	<b>9342.270</b>	<b>9342.300</b>	<b>9342.244</b>	<b>9342.274</b>	
<b>Accessories</b>								
Laminated copper bars		–	■	■	■	■	■	314