

TopTherm wall-mounted cooling units "Blue e"



Climate control accessories Page 369 Therm software Page 385

Temperature control:

- e-Comfort controller (factory setting +35°C)

Protection category IP to IEC 60 529:

- External circuit IP 34
- Internal circuit IP 54

Supply includes:

- Nano-coated condenser
- Fully wired ready for connection (plug-in terminal strip)
- Drilling template
- Assembly parts

Approvals:


Available on the Internet

Performance diagrams:

Available on the Internet

Technical details:

Available on the Internet



Output class 500 W

Model No.	Packs of	3303.500	3303.510	3303.600	Page
Material	Sheet steel	■	■	-	
	Stainless steel	-	-	■	
Colour	RAL 7035	■	■	-	
Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW		0.55	-	0.55	
Total cooling output 50/60 Hz L35 L35 kW		0.55 / 0.66	0.66	0.55 / 0.66	
Total cooling output 50/60 Hz L35 L50 kW		0.33 / 0.4	0.4	0.33 / 0.4	
Rated operating voltage V, ~, Hz		230, 1~, 50/60	115, 1~, 60	230, 1~, 50/60	
Width (B) mm		280	280	280	
Height (H) mm		550	550	550	
Depth (T) mm		210	210	210	
Rated current max. A		2.6 / 2.6	5.7	2.6 / 2.6	
Start-up current A		5.1 / 6.4	11.5	5.1 / 6.4	
Pre-fuse A		10	10	10	
Power consumption P _{el} 50/60 Hz L35 L35 kW		0.39 / 0.41	0.5	0.39 / 0.41	
Power consumption P _{el} 50/60 Hz L35 L50 kW		0.45 / 0.42	0.53	0.45 / 0.42	
Operating temperature range		+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511		1.4	1.31	1.4	
Refrigerant g		R134a, 170	R134a, 170	R134a, 170	
Permissible operating pressure (p. max.) bar		28	28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m ³ /h		265 / 315	280 / 345	265 / 315	
Weight kg		17.0	17.0	17.0	
Accessories					
Filter mats	3 pc(s).	3286.300	3286.300	3286.300	369
Metal filters	1 pc(s).	3286.310	3286.310	3286.310	370
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	639
Condensate hose	1 pc(s).	3301.610	3301.610	3301.610	377