


Air/water heat exchangers

Output class 600 – 1000 W, wall-mounted

Model No.	Packs of	3214.100	3364.504	3364.100	3364.500	Page
Water-carrying parts	Copper/brass (Cu/CuZn)	■	–	■	■	
	Stainless steel (1.4571)	–	■	–	–	
Temperature control	Basic controller (factory setting +35°C)	–	–	■	–	
	e-Comfort controller (factory setting +35°C)	–	■	–	■	
	Thermostat-controlled magnetic valve	■	–	–	–	
Total cooling output L35 W10, 200 l/h kW		0.6	–	–	–	
Total cooling output L35 W10, 400 l/h kW		0.7	0.95	1	1	
Rated operating voltage V, ~, Hz		230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	
Width mm		200	280	280	280	
Height mm		500	550	550	550	
Depth mm		100	120	120	120	
Power consumption P _{el} 50/60 Hz W		36 / 37	37 / 38	37 / 38	37 / 38	
Rated current max. A		0.17 / 0.18	0.18 / 0.18	0.18 / 0.18	0.18 / 0.18	
Pre-fuse A		2	4	4	4	
Operating temperature range		+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Water inlet temperature		+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	
Water connection	½" connector sleeve	■	■	■	■	
	G ¾" external thread	–	■	■	■	
Permissible operating pressure (p. max.) bar		1 - 10	1 - 10	1 - 10	1 - 10	
Air throughput of fans (unimpeded air flow) m³/h		280 / 310	290 / 345	290 / 345	290 / 345	
Weight kg		7.0	9.0	9.0	9.0	
Accessories						
Condensate hose	1 pc(s).	3301.612	3301.612	3301.612	3301.612	377
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	639
Toroidal transformer, primary connection 115 V/400 V		see page	see page	see page	see page	382
Fitting G ¾"	2 pc(s).	–	3201.900	3201.900	3201.900	378
Flow regulator valve		see page	see page	see page	see page	378
Digital enclosure internal temperature display and thermostat		–	–	–	–	
SK BUS system	1 pc(s).	–	3124.100	–	3124.100	382
Interface board	1 pc(s).	–	3124.200	–	3124.200	381

Accessories



Therm software

see page 385