



Climate control accessories Page 369 Chillers Page 361 Roof plates TS with mounting cut-out Page 383 Air routing Page 374

Colour:

– RAL 7035

Protection category IP to IEC 60 529:

– IP 55

Cooling medium:

– Water (see Internet for specifications)

Supply includes:

- Fully wired ready for connection (plug-in terminal strip)
- Drilling template
- Sealing mat
- Assembly parts

Approvals:

Available on the Internet

Performance diagrams:

Available on the Internet

Technical details:

Available on the Internet

Output class 1875 – 4000 W, roof-mounted

Model No.	Packs of	3209.504	3209.100	3209.500	3210.504	3210.100	3210.500	Page
Water-carrying parts	Copper/brass (Cu/CuZn)	–	■	■	–	■	■	
	Stainless steel (1.4571)	■	–	–	■	–	–	
Temperature control	Basic controller (factory setting +35°C)	–	■	–	–	■	–	
	e-Comfort controller (factory setting +35°C)	■	–	■	■	–	■	
Total cooling output L35 W10, 400 l/h kW		1.88	2.5	2.5	3	4	4	
Rated operating voltage V, ~, Hz		230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	230, 1~, 50/60	
Width mm		597	597	597	597	597	597	
Height mm		417	417	417	417	417	417	
Depth mm		475	475	475	475	475	475	
Power consumption P _{el} 50/60 Hz W		95 / 110	95 / 110	95 / 110	100 / 120	100 / 120	100 / 120	
Rated current max. A		0.4 / 0.48	0.4 / 0.48	0.4 / 0.48	0.44 / 0.5	0.44 / 0.5	0.44 / 0.5	
Pre-fuse A		4	4	4	4	4	4	
Operating temperature range		+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	+1°C...+70°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Water inlet temperature		+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	+1°C...+30°C	
Water connection	½" connector sleeve	■	■	■	■	■	■	
	G ¾" external thread	■	■	■	■	■	■	
Permissible operating pressure (p. max.) bar		1 - 10	1 - 10	1 - 10	1 - 10	1 - 10	1 - 10	
Air throughput of fans (unimpeded air flow) m³/h		925 / 1030	925 / 1030	925 / 1030	815 / 925	815 / 925	815 / 925	
Weight kg		23.5	23.5	23.5	25.5	25.5	25.5	

Accessories

Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	4127.010	4127.010	639
SK BUS system	1 pc(s).	3124.100	–	3124.100	3124.100	–	3124.100	382
Interface board	1 pc(s).	3124.200	–	3124.200	3124.200	–	3124.200	381
Air duct system	1 pc(s).	3286.870	3286.870	3286.870	3286.870	3286.870	3286.870	374
Stoppers	2 pc(s).	3286.880	3286.880	3286.880	3286.880	3286.880	3286.880	376
Condensate hose	1 pc(s).	3301.612	3301.612	3301.612	3301.612	3301.612	3301.612	377
Flow regulator valve		see page	see page	see page	see page	see page	see page	378