

Liquid Cooling Package



Climate control accessories Page 369 Chillers Page 361 Therm software Page 385

Air/water heat exchangers in TS 8 baying system, to fit 600 or 800 mm deep and 2000 mm high TS 8 enclosures. Air outlet either with 5 kW on each side or 10 kW on one side only. Options available for water connection on the top or bottom of the unit.

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 54

Cooling medium:

- Water (see Internet for specifications)

Supply includes:

- Fully wired ready for connection (plug-in terminal strip)
- Front door

Note:

- Bayable by screw-fastening at the sides

Performance diagrams:

Available on the Internet

Photo shows a configuration example with equipment not included in the scope of supply

Output class 10 kW, LCP Rack Industry

Model No.		Packs of	3378.200	3378.280	Page
Water-carrying parts	Copper/brass (Cu/CuZn)		■	■	
Total cooling output L35 W10, 2000 l/h kW			10	10	
Power consumption P _{el} 50/60 Hz W			704 / 816	704 / 816	
Rated operating voltage V, ~, Hz			230, 1~, 50/60	230, 1~, 50/60	
Width mm			300	300	
Height mm			2000	2000	
Depth mm			600	800	
Rated current max. A			3 / 3.5	3 / 3.5	
Pre-fuse A			4	4	
Operating temperature range			+5°C...+70°C	+5°C...+70°C	
Setting range			+20°C...+55°C	+20°C...+55°C	
Water inlet temperature			+7°C...+30°C	+7°C...+30°C	
Water connection	¾" connector sleeve		■	■	
	¾" internal thread		■	■	
Permissible operating pressure (p. max.) bar			1 - 10	1 - 10	
Air throughput of fans (unimpeded air flow) m³/h			2120 / 1960	2120 / 1960	
Weight kg			121.0	130.0	
Accessories					
Base/plinth components, front and rear, 100 mm		1 set(s)	8601.915	8601.915	513
Base/plinth trim panels, side, 100 mm		1 set(s)	8601.060	8601.080	514
Base/plinth components, front and rear, 200 mm		1 set(s)	8602.915	8602.915	513
Base/plinth trim panels, side, 200 mm		1 set(s)	8602.060	8602.080	514
Side panels, screw-fastened, sheet steel		2 pc(s).	8106.235	8108.235	534
Condensate hose		1 pc(s).	3301.612	3301.612	377