

1

Gleitplatten, selbstschmierend

Wear plates, self-lubricating



Plaques de frottement, autolubrifiantes



SN4173-

Mat.: Bronze
190-220 HB S10/3000
< 150 °C


SN4173-Form-
B1-L1



Form A



Form B



Form C



Form D

Form	B1	L1	L2	B3	D1	Anzahl Bohrungen Number of drillings Nombre de perçages	T
A	18	50	20	-	6,5	2	3,6
A	18	75	45	-	6,5	2	3,6
A	18	100	70	-	6,5	2	3,6
B	18	150	60	-	6,5	3	3,6
A	28	50	20	-	9	2	4,6
A	28	75	45	-	9	2	4,6
A	28	100	70	-	9	2	4,6
B	28	150	60	-	9	3	4,6
A	38	50	20	-	9	2	4,6
A	38	75	45	-	9	2	4,6
A	38	100	70	-	9	2	4,6
B	38	150	60	-	9	3	4,6
A	48	75	45	-	9	2	4,6
A	48	100	70	-	9	2	4,6
A	48	125	95	-	9	2	4,6
B	48	150	60	-	9	3	4,6
C	75	75	45	45	9	4	4,6
C	75	100	70	45	9	4	4,6
C	75	125	95	45	9	4	4,6
D	75	150	60	45	9	6	4,6
C	100	100	70	70	9	4	4,6
C	100	125	95	70	9	4	4,6
D	100	150	60	70	9	6	4,6