




**2/2 way solenoid valve normally closed or normally open  
type 20, brass body  
direct operated, DN 1,5 – 10,0 mm, G1/8 – G1/2**



normally closed NC



normally open NO



<b>SPECIFICATION</b>	
<b>general</b>	
type of construction	2/2-poppet valve, normally closed NC or normally open NO, coil 360° rotatable
operator	solenoid, or by manual override
ports	G1/8 – G1/2
ambient temperature	-20°C to +50°C, higher allowed ambient temperatures on request
fluid temperature	dependent on sealing material and coil
viscosity	max. 37 mm²/s (cst) or 5° E
material	body brass, inner parts brass and stainless steel, sealing - see type selection
mounting	installation into fixed piping systems or by use of 2 threads on the bottom side
installation	in any position, preferable vertical fixed solenoid coil
unit of supply	without connector
<b>electrical data</b>	
voltage	DC voltage or AC voltage
standard voltage	24V DC, 24V AC, 230V AC
special voltage on request	6V-200V DC, 12V-240V, 50Hz or 60Hz
acceptable voltage tolerance	+/- 10%
power consumption	see specifications at solenoid coils
coil type	temperature class F (155°C), winding class H (180°C), coil E3 temperature class H
duty cycle	100% ED (DB), continuous operation
protection class	IP65 according DIN EN 60529 (DIN 40050) with correctly mounted connector
<b>pneumatic – hydraulic</b>	
fluid	all liquids and gases, which don't attack the used material
max. body housing pressure	PN 64 (bar) up to DN 4mm, PN 25 (bar) from DN 5 – 10mm
response time	depending on operating pressure and fluid
special equipment on request	stainless steel AISI303 in place of brass, coil type with cable, bright nickel-plated or chemical nickel-plated, coils for temperature class H (180°C), higher differential pressure, PTFE seal

E &amp; OE: We reserve the right to change design, dimensions or materials without notice.

**type 20A, normally closed**

type * (order-nr.)	NW DN (mm)	ports	maximum differential pressure in bar **								kv-value (m³/h)
			coil <b>E1AA</b>		coil <b>E2AA</b>		coil <b>E3AE</b>		coil <b>EXFA</b>		
			~ (50Hz)	= (DC)	= (DC)	~ (50Hz)	= (DC)	~ (50Hz)	= (DC)	~ (50Hz)	= (DC)
20A-1.15-A...	1,5	G1/8	40	40				40	40		
20A-2.15-A...		G1/4									0,08
20A-1.20-A...	2,0	G1/8	35	35				35	35		
20A-2.20-A...		G1/4									0,13
20A-1.25-A...	2,5	G1/8	20	20	30	30	35	20	20		
20A-2.25-A...		G1/4									0,19
20A-1.30-A...	3,0	G1/8	12	12	25	23	28	16	12		
20A-2.30-A...		G1/4									0,25
20A-1.35-A...	3,5	G1/8	10	8	20	20	25	12	8		
20A-2.35-A...		G1/4									0,30
20A-1.40-A...	4,0	G1/8	6	4	14	17	22	7	3,5		
20A-2.40-A...		G1/4									0,37
20A-2.50-A...	5,0	G1/4									
20A-3.50-A...		G3/8	3,5	1	4	10	6	3	1	11	0,55
20A-4.50-A...		G1/2								12	
20A-2.60-A...	6,0	G1/4									
20A-3.60-A...		G3/8	0,9	0,5	1,9	3,5	2,5	1,4	0,4	7,5	0,67
20A-4.60-A...		G1/2								5	
20A-3.80-A...	8,0	G3/8	0,5	0,1	0,6	2	1	0,2	0,1	2,5	1,8
20A-4.80-A...	8,0	G1/2	0,5	0,1	0,6	2	1	0,2	0,1	2,5	1,70
20A-3.100-A...	10,0	G3/8	0,4	0,05	0,3	1,2	0,5	0,07	-	1,7	0,9
20A-4.100-A...	10,0	G1/2	0,4	0,05	0,3	1,2	0,5	0,07	-	1,7	0,9
											2,00

\* Type designation (order-nr.) must be completed with sealing material, short circuit ring, coil and supply voltage. (see order code)

\*\* At DC voltage all pressure specifications apply to a fluid temperature up to 80 °C. At higher fluid temperatures, the maximum differential pressure will be reduced by 0,4% / °C. All specifications refer to fluids with a maximum viscosity of 37 cst. (5°E).

Higher viscosities cause extended response time and need a special specification of the valve.

sealing material	Code	fluid temperature	applicable for
NBR (Perbunan)	B	max. 80°C	neutral gases and liquids
EPDM	E	max. 120°C	hot water, steam, not for oil and grease
FPM	V	max. 130°C	oil, petrol, oxygen

standard voltage	Code
24V = DC	<b>02400</b>
24V ~ (50Hz)	<b>02450</b>
230V ~ (50Hz)	<b>23050</b>

**coil power consumption at 20 °C, protection class, interface**

coil type	inrush power ~ (50Hz) VA	rated power ~ (50Hz) VA	power = (DC) (W)	protection class with/without connector	interface
E1AA	32	14	12	IP65 / IP00	Connector DIN EN 175301-803 (DIN 43650) type A
E2AA	-	-	17	IP65 / IP00	Connector DIN EN 175301-803 (DIN 43650) type A
E3AE	70	30	27	IP65 / IP00	Connector DIN EN 175301-803 (DIN 43650) type A
EXFA	9	9	10,3	IP65	Coil explosion proof according to ATEX II 2G Ex mb II T4, II 2D ExDA21 IP65 T130°C, cable length 3m
F1AA	70	30	27	IP65 / IP00	Connector DIN EN 175301-803 (DIN 43650) type A

order code	<b>20 B - 2 E 30 C Z - A E1AA 23050</b>	
	type	function
	function	short circuit ring
	ports	stroke compensation spring
	seal material	throw off spring
	nominal size seat	
	throw off spring	
	stroke compensation spring	
	short circuit ring	
	coil type	
	supply voltage	


type 20, direct operated, body brass, tube stainless steel  
A = normally closed, B = normally open  
1 = G 1/8, 2 = G1/4, 3 = G3/8, 4 = G1/2  
B = NBR (Perbunan), E = EPDM, V = FPM  
nominal size x 10 = specification for order code  
C,D,F = only normally open  
Z = only normally open  
A = copper short circuit ring, X = without short circuit ring  
see specifications of the particular coil  
always 5-digit, see code of standard voltage

**type 20B, normally open**

type * (order.-nr.)	NW DN (mm)	connection	maximum differential pressure in bar **					kv-value (m³/h)
			coil <b>E1AA</b>	coil <b>EXFA</b>	coil <b>E3AE</b>	coil <b>F1AA</b>		
			~ (50Hz) und = (DC)	~ (50Hz) und = (DC)	~ (50Hz) = (DC)	~ (50Hz) und = (DC)		
20B-1.15CZ-AE...	1,5	G1/8	35	35				0,08
20B-2.15CZ-AE...		G1/4						
20B-1.20CZ-AE...	2,0	G1/8	22	22				0,13
20B-2.20CZ-AE...		G1/4						
20B-1.25CZ-AE...	2,5	G1/8	13	13				0,19
20B-2.25CZ-AE...		G1/4						
20B-1.30CZ-AE...	3,0	G1/8	10,5	10,5				0,25
20B-2.30CZ-AE...		G1/4						
20B-1.35CZ-AE...	3,5	G1/8	6,5	6,5				0,30
20B-2.35CZ-AE...		G1/4						
20B-1.40CZ-AE...	4,0	G1/8	5,5	5,5				0,37
20B-2.40CZ-AE...		G1/4						
20B-2.50FZ-A...	5,0	G1/4				9	9	0,54
20B-3.50FZ-A...		G3/8						
20B-4.50FZ-A...		G1/2						
20B-2.60FZ-A...	6,0	G1/4				6	6	0,64
20B-3.60FZ-A...		G3/8						
20B-4.60FZ-A...		G1/2						

\* Type designation (order-nr.) must be completed with sealing material, coil and supply voltage.

\*\* Higher differential pressure on request.


**Dimension table for type 20 in mm, weight approx. in g**

G	coil	N	O	M	H	type 20A-	type 20B-	d	h	I	L	D	weight (approx. g) type 20A- type 20B-
G 1/8	E1	16	M4	55,1	79	86	30	10	7,5	42	25	370	390
	E2			57			35					436	456
	E3			56			36					456	476
	EX			54			38					710	730
	F1			57	90	93	38					526	516
G 1/4	E1			55,1	79	86	30	9	46	54	25	360	380
	E2			57			35					426	446
	E3			56			36					446	466
	EX			54			38					700	720
	F1			57	90	93	38					516	506
G 3/8	E1			55,1	79	86	30	12	10	46	54	380	400
	E2			57			35					446	466
	E3			56			36					466	486
	EX			54			38					720	740
G 1/2	F1			57	90	93	38					536	526
	E1			55,1	79	86	30					390	410
	E2			57			35					456	476
	E3			56			36					476	496
	EX			54			38					730	750
	F1			57	90	93	38					546	536