


SERIES 67



SOLID HIGH TEMPERATURE THERMOSETTING RESIN WHEELS FIXED BRACKET TYPE "NL"


Wheel description



Tread: solid high temperature thermosetting resin wheels, resistant to temperatures from -20°C and +300°C.
Hub: the plain bearing bore results from a hole in the material forming the centre of the wheel and contains the axle.

Bracket description

Standard duty bracket type NL (max. carrying capacity 400 daN)



The bracket is made by an electrolytically galvanised steel fork.