

SERIES 71



**GREY NON-MARKING THERMOPLASTIC RUBBER WHEELS,
POLYPROPYLENE CENTRE,
SWIVEL BOLT HOLE BRACKET TYPE "SL"**

Wheel description




Tread: grey non-marking thermoplastic rubber tread, hardness 85+/-4 Shore A; excellent rolling resistance and elasticity.

Centre: polypropylene.

Hub: the hub is available with plain bearing, with roller bearing and with double shielding ball bearing, coprinted in the centre of the wheel.

Bracket description

Standard duty bracket type SL (max. carrying capacity 120 daN)



1) **Plate:** electrolytically galvanised steel plate

2) **Fork:** electrolytically galvanised steel plate

3) **Ball Racing Ring:** electrolytically galvanised steel plate

4) **King Pin:** incorporated in top plate and cold riveted

5) **Swivel actions:** double ring of greased balls

Finishing: electrolytic galvanisation

Fitting: bolt hole