




VR*-I CHECK VALVES SERIES 32

CARTRIDGE TYPE


p max (see table of performances)

Q max (see table of performances)

PRESSURE DROPS AP-Q



OPERATING PRINCIPLE




- VR*-I valves are one-way check valves with spring, cartridge type, that can be used in blocks or panels.
- In rest conditions, the valve poppet, which is a cone on edge seal type, is kept closed by a spring with fixed setting.
- The poppet opens when the pressure at the inlet port "A" exceeds the set value of the spring, additional to any pressure in the outlet port "B".
- Available in three sizes for flow rates of up to 300 l/min.
 Three cracking pressures values available.
- The zinc-nickel finishing treatment makes the VR*-I suitable to withstand exposure to salt spray for 600 hours. (value established according to UNI EN ISO 9227 and UNI EN ISO 10289)

PERFORMANCES

valve code	code dimension flow r	maximum flow rate	mass [kg]	max operating pressure [bar]	
5546		[l/min]		continuous	peak
VR2-I	1/4"	50	0,1	320	320
VR5-I	3/4"	150	0,2	250	320
VR7-I	11⁄4"	300	0,8	230	320


Ambient temperature range	°C	-20 / +60	
Fluid temperature range	°C	-20 / +80	
Fluid viscosity range	cSt	10 ÷ 400	
Fluid contamination degree	according to ISO 4406:1999 class 20/18/15		
Recommended viscosity	cSt	25	
Surface finishing	zinc-nickel surface treatment		

HYDRAULIC SYMBOL



45 100/121 ED 1/2

1 - IDENTIFICATION CODE




2 - HYDRAULIC FLUIDS

Use mineral oil-based hydraulic fluids HL or HM type, according to ISO 6743-4. For these fluids, use NBR seals. For fluids HFDR type (phosphate esters) use FPM seals (code V). For the use of other kinds of fluid such as HFA, HFB, HFC, please consult our technical department. Using fluids at temperatures higher than 80 °C causes a faster degradation of the fluid and of the seals characteristics.

The fluid must be preserved in its physical and chemical characteristics.

3 - OVERALL AND MOUNTING DIMENSIONS





DUPLOMATIC MS S.p.A.

via M. Re Depaolini 24 • 20015 PARABIAGO (MI) • ITALY tel. +39 0331.895.111 • www.duplomatic.com • e-mail: sales.exp@duplomatic.com